


Designed by Komplot Design

PRODUCT





DESCRIPTION

The GUBI Chair Collection is a chair series in laminated moulded 3-D veneer or in the injection moulded HiRek material. The shell is 5 mm thick. Both types of the shells can be delivered upholstered, with front upholstered or fully upholstered in fabric or leather. The base is available in steel, in different finishes as specified below and moulded wood in various finishes. Several of the chair versions are stackable. The GUBI Chair series includes a side chair with and without arms, a bar stool, a lounge chair and a table series in 3 different heights.

VERSION - HIREK (PP PLASTIC MATERIAL)

RAL codes are indicative.

- Black // RAL 9005, silkmatt /
- Venetian Gold // RAL 080 7050 , silkmatt /
- Mistletoe Green // RAL 130 5010, silkmatt /
- Nightfall Blue // RAL 200 7005, silkmatt /
- Rainy Gray // RAL 7031, silkmatt /
- White Cloud // RAL 9001, silkmatt /Moon Gray // RAL 085 7010, silkmatt /
- Shy Cherry // RAL 3011, silkmatt /
- Black painted base // RAL 9005, gloss level 10-15
- Chrome base // Mirror chrome

CHAIR VERSION

Order item - look for part number in the pricelist.

The series consists of the following:

GUBI 3F, GUBI 32F, GUBI 33F

COLOURS



// Venetian Gold

FACTS

// White Cloud

MEASUREMENT - L X W X H MM

Sitting height: 750 mm
Seat width: 401 mm
Seat depth: 416 mm
Seat height: 147 mm
Back height: 163 mm
Frame width: 420 mm
Frame depth: 430 mm
Chair height: 880 mm
Shell thickness: 5 mm

Frame thickness: Ø11 mm

Footrest height: 200 mm

WEIGHT ITEM 4,2 kg

PACKAGING TYPE Cardboard box

PACKAGING MEASUREMENT - $L \times W \times H \times CM$ L:44 X W:44 X H:80 CM

WEIGHT PACKAGING - MATERIAL TYPE

- Delivery note: 5 g
- Cardboard box, FEFCO quality EB85BB: 1485 g
- Cardboard extra bottom: 272 g
- Polybag PE: 158 g
- LD-EPE foam protector: 44 g
- Strapping: 7 g

WEIGHT PACKAGING - *TOTAL* 6,851 kg

NUMBER OF PARCELS 1 pcs.

- Defective frame and shells can be replaced.



ACCESSORIES

FELT GLIDERS FOR HARD FLOOR AVAILABLE ON REQUEST.

LINKING DEVICE



CLEANING AND MAINTENANCE

For dusting and light cleaning of the plastic surface and frame use a soft, dry cloth.

For further cleaning, use a soft cloth that is firmly wrung in clean water for gently wiping the surface, and then immediately use a dry cloth to wipe the surface again.

If more thorough cleaning is necessary, use a mild detergent or washing-up liquid dissolved in water on a firmly wrung cloth. Afterwards, repeat the process with clean water as described above. Polish with a soft cloth after wiping.

Do not use materials for maintenance that:

- · Contain abrasive agents.
- Are basic, acidiferous or organic.

For the best maintenance of the product, protect it against sunlight and heat, and try to keep it away from moisture, grease and other dirt.

Furthermore, protect the surfaces against sharp objects and other that might scratch.

ENVIRONMENT

Parts can be separated and sorted for recycling.

Disposal of plastic type PP may be done with incineration of waste.

TESTS

-

CERTIFICATION AND LABELS

-